


ME-IO-S FE CONTACT SMT - Functional ground contact



1569960

<https://www.phoenixcontact.com/us/products/1569960>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Functional ground contact, for ME-IO-S series electronics housings

Your advantages

- Easy installation

Commercial data

Item number	1569960
Packing unit	200 pc
Minimum order quantity	100 pc
Sales key	AC15
Product key	ACHEBF
GTIN	4067923057258
Weight per piece (including packing)	1.1 g
Weight per piece (excluding packing)	1.1 g
Customs tariff number	85369095
Country of origin	CN

ME-IO-S FE CONTACT SMT - Functional ground contact



1569960

<https://www.phoenixcontact.com/us/products/1569960>

Technical data

Notes

Recommendation	Further information and detailed dimensions are available in the download area.
----------------	---

Product properties

Product type	Ground contact
Housing type	DIN rail housing
Housing type	Multifunctional housings
Housing series	ME-IO-S
Product family	ME-IO-S..

Dimensions

Width	5.5 mm
Height	2.8 mm
Depth	14 mm

Material specifications

Color	silver-colored
Material Contact	Cu alloy
Surface characteristics	Tin-plated

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 Hz ... 60.1 Hz)
Acceleration	5g (60.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

ME-IO-S FE CONTACT SMT - Functional ground contact



1569960

<https://www.phoenixcontact.com/us/products/1569960>

Ambient temperature (operation)	-40 °C ... 70 °C (No rise in temperature)
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Mounting

Mounting type	THR soldering
---------------	---------------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

ME-IO-S FE CONTACT SMT - Functional ground contact



1569960

<https://www.phoenixcontact.com/us/products/1569960>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

ME-IO-S FE CONTACT SMT - Functional ground contact



1569960

<https://www.phoenixcontact.com/us/products/1569960>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com