

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, irradiated, orange RAL 2003, Plug straight M12, coding: A, on Socket straight M8, cable length: 0.6 m

As shown in the illustration but with an orange conductor

Commercial data

Item number	1574768
Packing unit	5 pc
Minimum order quantity	50 pc
Product key	AF1COA
GTIN	4046356432184
Weight per piece (including packing)	60.47 g
Weight per piece (excluding packing)	60.47 g
Country of origin	PL

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Technical data

Product properties

Product type	Distributor with cable
Number of positions	3
No. of cable outlets	2
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M12
Number of positions	3
Coding type	A

Connection 2

Type	Socket straight M8
------	--------------------

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768


<https://www.phoenixcontact.com/us/products/1574768>

Number of positions	3
---------------------	---

Cable/line

Cable length	0.6 m
--------------	-------

PUR irradiated halogen-free orange [150]

Dimensional drawing	
Number of positions	3
Shielded	no
Cable type	PUR irradiated halogen-free orange [150]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.05 mm ±0.05 mm (Signal line)
External cable diameter	4.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Max. conductor resistance	max. 57 Ω/km
Nominal voltage, cable	250 V (AC)
Test voltage	2000 V (50 Hz, 5 minutes)
Smallest bending radius, fixed installation	13.5 mm
Smallest bending radius, movable installation	53 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 44 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Flame resistance	according to DIN VDE 0472 Part 804
Other resistance	UV resistant
Special properties	Silicone-free Irradiated
Ambient temperature (operation)	-50 °C ... 105 °C (cable, fixed installation) -40 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-50 °C ... 105 °C (cable, fixed installation)
	-40 °C ... 105 °C (Cable, flexible installation)

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Drawings

Dimensional drawing



Plug M12 x 1, Y distributor

Dimensional drawing



Socket M8 x 1, straight

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Schematic diagram



Pin assignment M12 Y plug, 4-pos., A-coded, view plug side

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable

1574768

<https://www.phoenixcontact.com/us/products/1574768>

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

Circuit diagram



Contact assignment of M12 plugs / M8 sockets

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Classifications

ECLASS

ECLASS-13.0	27060313
ECLASS-15.0	27060313

SAC-3P-M12Y/2X0,6-150/M 8FS PF - Sensor/actuator cable



1574768

<https://www.phoenixcontact.com/us/products/1574768>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com