

# VL3 FPM 215 - Monitor

1580715

<https://www.phoenixcontact.com/us/products/1580715>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VL3 FPM 215 is a 21.5-inch, 1920 x 1080, industrial touch, IP66-rated, flat panel monitor with the look and dimensions of the WP 6.../TP 6... and VL3 PPC.

## Product description

The Valueline VL3 FPM is an industrial, flat-panel monitor for use in applications where a remote display location is required.

## Your advantages

- 21.5" display
- DisplayPort, VGA, and HDMI input ports
- 2x USB Ports for Keyboard & Mouse use
- Ambient operating temperatures from -20 °C ... 60 °C

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1580715       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR12          |
| Product key                          | DRBAAD        |
| GTIN                                 | 4067923070691 |
| Weight per piece (including packing) | 11,100 g      |
| Weight per piece (excluding packing) | 7,400 g       |
| Country of origin                    | TW            |

# VL3 FPM 215 - Monitor

1580715

<https://www.phoenixcontact.com/us/products/1580715>



## Technical data

### Notes

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|              |         |
|--------------|---------|
| Product type | Monitor |
|--------------|---------|

#### Computer data

|        |         |
|--------|---------|
| Extras | without |
|--------|---------|

#### Display

|                       |                               |
|-----------------------|-------------------------------|
| Display type          | 54.6 cm / 21.5"-TFT           |
| Screen resolution     | 1920 x 1080 Pixel(s)          |
| Display formats       | 16:9                          |
| Touch technology      | Capacitive multi-touch screen |
| Display lighting type | LED                           |
| Brightness            | 400 cd/m <sup>2</sup>         |
| MTBF                  | 50000 h                       |
| Color spectrum        | 16.7 million colors           |

### Electrical properties

#### Supply

|                          |                   |
|--------------------------|-------------------|
| Supply voltage           | 24 V DC $\pm$ 20% |
| Max. current consumption | 1.4 A (24 V DC)   |

### Connection data

#### Power supply

|                                |                                             |
|--------------------------------|---------------------------------------------|
| Connection method              | Push-in technology                          |
| Conductor cross-section, rigid | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG    | 24 ... 16                                   |
| Stripping length               | 30 mm                                       |

### Interfaces

|            |                                        |
|------------|----------------------------------------|
| Interfaces | 1x USB Type A (For touch control only) |
|            | 1x DisplayPort                         |
|            | 1x HDMI                                |
|            | 1x VGA                                 |

### Dimensions

#### External dimensions

|                        |                   |
|------------------------|-------------------|
| Width / Height / Depth | 532 mm / 346 mm / |
|------------------------|-------------------|

#### Installation dimensions

# VL3 FPM 215 - Monitor



1580715

<https://www.phoenixcontact.com/us/products/1580715>

|                                     |                                        |
|-------------------------------------|----------------------------------------|
| Width / Height / Installation depth | 522 mm / 336 mm / 52 mm (Panel cutout) |
|-------------------------------------|----------------------------------------|

## Material specifications

|                 |                            |
|-----------------|----------------------------|
| Color (Housing) | white aluminium (RAL 9006) |
|-----------------|----------------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                              |
|------------------------------------------|----------------------------------------------|
| Degree of protection                     | IP66 (front (panel mount))                   |
|                                          | IP30 (back/all around when VESA installed)   |
| Ambient temperature (operation)          | -20 °C ... 60 °C                             |
| Ambient temperature (storage/transport)  | -40 °C ... 70 °C                             |
| Altitude                                 | ≤ 2000 m                                     |
| Permissible humidity (operation)         | 10 % ... 95 % (non-condensing)               |
| Permissible humidity (storage/transport) | 10 % ... 95 % (non-condensing)               |
| Shock                                    | 15g, 11 ms in accordance with IEC 60068-2-27 |
| Vibration (operation)                    | 1g, according to EN 60068-2-6                |

## Mounting

|               |                                           |
|---------------|-------------------------------------------|
| Mounting type | Panel cutout                              |
|               | VESA holder                               |
| Holder system | VESA MIS-D 100 C (Voids UL 61010 listing) |

# VL3 FPM 215 - Monitor



1580715

<https://www.phoenixcontact.com/us/products/1580715>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1580715>

|                                                                                   |                                                          |
|-----------------------------------------------------------------------------------|----------------------------------------------------------|
|  | <b>IECEE CB Scheme</b><br>Approval ID: US-45363-UL       |
|  | <b>cULus Listed</b><br>Approval ID: E238705-D1066 UL CoC |
|  | <b>cULus Listed</b><br>Approval ID: E196811-20250620     |

# VL3 FPM 215 - Monitor

1580715

<https://www.phoenixcontact.com/us/products/1580715>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19200201 |
| ECLASS-15.0 | 19200201 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC004862 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# VL3 FPM 215 - Monitor

1580715

<https://www.phoenixcontact.com/us/products/1580715>



## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-15                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                      |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)