# HC-B 16-SFZ-84/O1M32 - Housing

1584619

https://www.phoenixcontact.com/us/products/1584619

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON box mounting base B16, for main latch, height 84 mm, with support 1xM32

## Commercial data

| | |
|---|---|
| Item number | 1584619 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF55 |
| Product key | AF7AAC |
| GTIN | 4046356145787 |
| Weight per piece (including packing) | 407.71 g |
| Weight per piece (excluding packing) | 407.71 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

## Technical data


### Notes

| | |
|---|---|
| General | For contact inserts HC-B16, BB32, BBB40, D40, DD72, HS6, M, K |

### Product properties

| | |
|---|---|
| Product type | Housing with locking latch |
| Housing type | Surface mounting housing |
| Application | Standard |
| Type | B16 |
| No. of cable outlets | 1 |
| Type of the screw connection | 1x M32 |
| Cable outlet | lateral |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 57 mm |
| Height | 84 mm |
| Length | 117 mm |

### Material specifications

| | |
|---|---|
| Seal material | NBR |
| Housing material | Die-cast aluminum |
| Housing surface material | Powder-coated, gray |

### Mechanical properties

Mechanical data

| | |
|---|---|
| Type of the screw connection | 1x M32 |

### Mounting

| | |
|---|---|
| Assembly note | For half and full screw connections |


### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP65 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

## Drawings

Dimensional drawing




Dimensional drawing

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261501 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com