# HC-B 16-SFQD-67/M1M25 - Housing

1586918

https://www.phoenixcontact.com/us/products/1586918

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Box mounting base for double locking latch, height 67 mm, with screw connection, 1x M25

## Commercial data

| | |
|---|---|
| Item number | 1586918 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Product key | AF7AAC |
| GTIN | 4046356427005 |
| Weight per piece (including packing) | 386.21 g |
| Weight per piece (excluding packing) | 386.21 g |
| Country of origin | DE |

## Technical data


### Notes

| | |
|---|---|
| General | For contact inserts HC-B16, BB32, BBB40, D40, DD72, HS6, M, K |

### Product properties

| | |
|---|---|
| Product type | Housing with locking latch |
| Housing type | Surface mounting housing |
| Application | Standard |
| Type | B16 |
| No. of cable outlets | 1 |
| Type of the screw connection | 1x M25 |
| Protective cover | yes |
| Shielded | no |
| Cable outlet | Left (view of the opened protective cover) |
| Pg screw connection | with |

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 57 mm |
| Height | 67 mm |
| Length | 117 mm |
| Wrench size, union nut | 25 mm |

### Material specifications

| | |
|---|---|
| Material Screw connection | Brass, nickel-plated |
| Material Protective cover | PA |
| Material grommet GRP | NBR |
| Housing material | Die-cast aluminum |
| Housing surface material | Powder-coated, gray |

### Mechanical properties

Mechanical data

| | |
|---|---|
| Type of the screw connection | 1x M25 |
| Locking type | Latch |

### Cable/line

| | |
|---|---|
| External cable diameter Cable 1 | 9 mm ... 18 mm |

## Connection data

| | |
|---|---|
| External cable diameter | 9 mm ... 18 mm |


## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Degree of protection | IP65 (When plugged in) |
| Ambient temperature (operation) | -40 °C ... 125 °C |

## Drawings

Dimensional drawing




Dimensional drawing

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261501 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com