

HC-26P1N12RQDU - Cable connector



1590301

<https://www.phoenixcontact.com/us/products/1590301>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, number of positions: 26, connection method: Solder connection, series: HC

Commercial data

Item number	1590301
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAJA
GTIN	4046356369053
Weight per piece (including packing)	144.22 g
Weight per piece (excluding packing)	144.22 g
Country of origin	DE

HC-26P1N12RQDU - Cable connector



1590301

<https://www.phoenixcontact.com/us/products/1590301>

Technical data

Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Type of the screw connection	Double bracket
Coding	N
Thread type	M27

Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A
Nominal voltage U _N	150 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Solder connection
Contact connection type	Pin

Mechanical properties

Mechanical data

Type of the screw connection	Double bracket
Insertion/withdrawal cycles	50

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

HC-26P1N12RQDU - Cable connector



1590301

<https://www.phoenixcontact.com/us/products/1590301>

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

HC-26P1N12RQDU - Cable connector




1590301

<https://www.phoenixcontact.com/us/products/1590301>

Drawings

Schematic diagram



Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com