

HC-28S1N12RNDU - Cable connector



1590437

<https://www.phoenixcontact.com/us/products/1590437>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 26-pos.
product version

Cable connector, application: Signal, straight, Screw locking mechanism, M27, contact connection type: Socket, number of positions: 28, connection method: Solder connection, series: HC

Commercial data

Item number	1590437
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAJA
GTIN	4046356187619
Weight per piece (including packing)	97.85 g
Weight per piece (excluding packing)	97.85 g
Country of origin	DE

HC-28S1N12RNDU - Cable connector



1590437

<https://www.phoenixcontact.com/us/products/1590437>

Technical data

Product properties

Product type	Circular connector (cable-side)
Series	HC
Application	Signal
Number of positions	28
Type of the screw connection	Pg16
Coding	N
Thread type	M27

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Electrical properties

Contact

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	150 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Mechanical properties

Mechanical data

Type of the screw connection	Pg16
------------------------------	------

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

HC-28S1N12RNDU - Cable connector

1590437

<https://www.phoenixcontact.com/us/products/1590437>



Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com