

# NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: NC, straight with plastic cover, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, Crimp connection, shielded: yes, cable diameter range: 2 mm... 10.5 mm, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %). This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1592030
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB35
Product key	ABRIEA
GTIN	4046356190244
Weight per piece (including packing)	40.59 g
Weight per piece (excluding packing)	36.14 g
Customs tariff number	85389099
Country of origin	DE

# NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

## Technical data

### Product properties

Product type	Circular connector housing
Series	NC
Application	Signal
Connection profile	12
Shielded	yes
Thread type	M23

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Rotating parts	CuZn
Seal material	FPM or NBR or EPDM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn), plastic parts: SPS
Gasket and O-ring material	NBR

### Connector

Type	straight with plastic cover
------	-----------------------------

### Cable/line

External cable diameter	2 mm ... 10.5 mm
-------------------------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)