

RC-0000000C0FZ - Housing for circular connector



1592790

<https://www.phoenixcontact.com/us/products/1592790>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RC, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket/pin, Crimp connection, Flat gasket, shielded: yes, panel thickness max.: 2.5 mm, cable diameter range: 2 mm... 10.5 mm. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1592790
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFK
GTIN	4046356192781
Weight per piece (including packing)	79.78 g
Weight per piece (excluding packing)	74.86 g
Customs tariff number	85366990
Country of origin	DE

RC-0000000C0FZ - Housing for circular connector



1592790

<https://www.phoenixcontact.com/us/products/1592790>

Technical data

Product properties

Product type	Circular connector housing
Series	RC
Application	Signal
Connection profile	12
Shielded	yes
Thread type	M23

Connection data

Connection method	Crimp connection
-------------------	------------------

Dimensions

Dimensional drawing	
Panel thickness	< 2.5 mm

Material specifications

Material Housing	GD-Zn
Material Rotating parts	CuZn
Material Housing surface	Ni
Material Seal	FPM (O-ring)
Seal material	FPM or NBR or EPDM

Connector

Type	straight
------	----------

Cable/line

External cable diameter	2 mm ... 10.5 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

Mounting


Mounting type	Rear mounting/square flange (4x M2,5)
---------------	---------------------------------------

RC-0000000C0FZ - Housing for circular connector

1592790

<https://www.phoenixcontact.com/us/products/1592790>

Drawings



Installation dimensions

RC-0000000C0FZ - Housing for circular connector



1592790

<https://www.phoenixcontact.com/us/products/1592790>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1592790

<https://www.phoenixcontact.com/us/products/1592790>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	26739219-b0f2-4067-b03c-c36264d9b99e

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com