

RC-0000000T0FZ - Housing for circular connector



1592992

<https://www.phoenixcontact.com/us/products/1592992>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RC, angled, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, Crimp connection, shielded: yes, cable diameter range: 2 mm... 10.5 mm. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1592992 |
| Packing unit | 8 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAFE |
| GTIN | 4046356193689 |
| Weight per piece (including packing) | 141.4 g |
| Weight per piece (excluding packing) | 130.255 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

RC-0000000T0FZ - Housing for circular connector



1592992

<https://www.phoenixcontact.com/us/products/1592992>

Technical data

Product properties

| | |
|--------------------|----------------------------|
| Product type | Circular connector housing |
| Series | RC |
| Application | Signal |
| Connection profile | 12 |
| Shielded | yes |
| Thread type | M23 |

Connection data

| | |
|-------------------|------------------|
| Connection method | Crimp connection |
|-------------------|------------------|

Material specifications

| | |
|--------------------------|--------------------|
| Material Housing | GD-Zn |
| Material Rotating parts | CuZn |
| Material Housing surface | Ni |
| Material Seal | FPM (O-ring) |
| Seal material | FPM or NBR or EPDM |

Connector

| | |
|------|--------|
| Type | angled |
|------|--------|

Cable/line

| | |
|-------------------------|------------------|
| External cable diameter | 2 mm ... 10.5 mm |
|-------------------------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -20 °C ... 125 °C |
| Altitude | 2000 m |

RC-0000000T0FZ - Housing for circular connector



1592992

<https://www.phoenixcontact.com/us/products/1592992>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440224 |
| ECLASS-15.0 | 27440224 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003556 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

1592992

<https://www.phoenixcontact.com/us/products/1592992>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | faf0e1ec-7019-49e8-8bd9-5719a3b74702 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com