

RC-06P1N8A1600 - Crimp contact



1593418

<https://www.phoenixcontact.com/us/products/1593418>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimp contact



The figure shows the 12-pos. product version

Commercial data

Item number	1593418
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356196062
Weight per piece (including packing)	78.71 g
Weight per piece (excluding packing)	78.71 g
Country of origin	DE

RC-06P1N8A1600 - Crimp contact



1593418

<https://www.phoenixcontact.com/us/products/1593418>

Technical data

Notes

Order information:	Order crimp contacts Ø 2 mm separately
Order information:	Order cable glands separately

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

RC-06P1N8A1600 - Crimp contact



1593418

<https://www.phoenixcontact.com/us/products/1593418>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-06P1N8A1600 - Crimp contact



1593418

<https://www.phoenixcontact.com/us/products/1593418>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com