

# RC-06S1NS280LB - Cable connector



1594195

<https://www.phoenixcontact.com/us/products/1594195>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, straight, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Screw connection, cable diameter range: 3 mm ... 10.5 mm, coding: N

The figure shows the 12-pos.  
product version

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1594195                        |
| Packing unit                         | 20 pc                          |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ABRAFA                         |
| GTIN                                 | 4046356200202                  |
| Weight per piece (including packing) | 73.93 g                        |
| Weight per piece (excluding packing) | 73.93 g                        |
| Country of origin                    | DE                             |

# RC-06S1NS280LB - Cable connector



1594195

<https://www.phoenixcontact.com/us/products/1594195>

## Technical data

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|   |  |
|---|--|
| Coding  | N  |
| Material (Insulating body)                      | PBT                                      |
| Material (Contact)                              | CuZn                                     |
| Material (Contact surface)                      | Ni/Au                                    |
| Insertion/withdrawal cycles                     | 50                                       |
| Connection method                               | Screw connection                         |
| Contact switching type                          | Socket                                   |
| Application                                     | Signal                                   |
| Number of positions                             | 6  |
| Direction of rotation                           | Standard                                 |
| Connection profile                              | 6  |
| Number (Contact group 1)                        | 6  |
| Contact diameter (Contact group 1)              | 2 mm                                     |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>                     |
| Litz wires Max. cross section (Contact group 1) | 1 mm <sup>2</sup>                        |
| Rated current Contact (Contact group 1)         | 20 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC                       |
| Rated surge voltage                             | 1.5 kV                                   |
| Overvoltage category                            | III                                      |
| Degree of pollution                             | 3  |

#### Housing

|                                   |                                  |
|-----------------------------------|----------------------------------|
| Note                              | Order contact inserts separately |
| Type                              | Cable connector housing          |
| Thread type                       | M23                              |
| Design                            | straight                         |
| Type of locking                   | Screw locking mechanism          |
| Pg screw connection               | none                             |
| Material (Housing)                | Metal                            |
| Degree of protection (plugged in) | IP65<br>IP67<br>IP68             |

#### Seal

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 3 mm ... 10.5 mm |
| Seal material           | NBR              |

# RC-06S1NS280LB - Cable connector



1594195

<https://www.phoenixcontact.com/us/products/1594195>

## Environmental product compliance

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)