

RC-09S1N8A80EN - Cable connector



1596350

<https://www.phoenixcontact.com/us/products/1596350>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Cable connector, application: Signal, straight, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 10.5 mm, coding: N

Commercial data

Item number	1596350
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356210775
Weight per piece (including packing)	73.945 g
Weight per piece (excluding packing)	69.05 g
Country of origin	DE

RC-09S1N8A80EN - Cable connector



1596350

<https://www.phoenixcontact.com/us/products/1596350>

Technical data

Notes

Order information:	Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65 IP67

RC-09S1N8A80EN - Cable connector



1596350

<https://www.phoenixcontact.com/us/products/1596350>

	IP68
Seal	
External cable diameter	3 mm ... 10.5 mm
Seal material	NBR

RC-09S1N8A80EN - Cable connector




1596350

<https://www.phoenixcontact.com/us/products/1596350>

Drawings

Schematic diagram



Connector pin assignment

RC-09S1N8A80EN - Cable connector

1596350

<https://www.phoenixcontact.com/us/products/1596350>

Schematic diagram



Connector pin assignment

RC-09S1N8A80EN - Cable connector



1596350

<https://www.phoenixcontact.com/us/products/1596350>

Classifications

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

RC-09S1N8A80EN - Cable connector



1596350

<https://www.phoenixcontact.com/us/products/1596350>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com