RC-12P1N12R2A5 - Crimp contact

1597309

https://www.phoenixcontact.com/us/products/1597309

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

The figure shows the 12-pos. product version, with double bracket strain relief

Crimp contact

Commercial data

Item number	1597309
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356215459
Weight per piece (including packing)	91.5 g
Weight per piece (excluding packing)	91.5 g
Country of origin	DE

Technical data

Product properties

Product type	Circular connector (cable-side)

Material specifications

Flammability rating according to UL 94	V0

Classifications

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com