

# RC-12P1N8A1200 - Cable connector



1597468

<https://www.phoenixcontact.com/us/products/1597468>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, coding: N

The figure shows the 12-pos. product version, with standard DIN cable gland

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1597468                        |
| Packing unit                         | 20 pc                          |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ABRAFA                         |
| GTIN                                 | 4046356216203                  |
| Weight per piece (including packing) | 72.16 g                        |
| Weight per piece (excluding packing) | 72.16 g                        |
| Country of origin                    | DE                             |

# RC-12P1N8A1200 - Cable connector



1597468

<https://www.phoenixcontact.com/us/products/1597468>

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Order information: | Order crimp contacts Ø 1 mm separately |
|--------------------|--|

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|   |   |
|---|---|
| Note                                    | Order information: Order crimp contacts Ø 1 mm separately |
| Coding                                  | N   |
| Material (Insulating body)              | PA 6.6  |
| Connection method                       | Crimp connection  |
| Contact switching type                  | Pin   |
| Application                             | Signal  |
| Number of positions                     | 12  |
| Direction of rotation                   | Standard  |
| Connection profile                      | 12  |
| Number (Contact group 1)                | 12  |
| Contact diameter (Contact group 1)      | 1 mm  |
| Rated current Contact (Contact group 1) | 8 A (for max. connection cross section)                   |
| Rated voltage Contact (Contact group 1) | 48 V AC<br>74 V DC  |
| Rated surge voltage                     | 1.5 kV  |
| Overvoltage category                    | III   |
| Degree of pollution                     | 3   |

#### Housing

|                                   |                         |
|-----------------------------------|-------------------------|
| Type                              | Cable connector housing |
| Thread type                       | M23                     |
| Design                            | straight                |
| Type of locking                   | Screw locking mechanism |
| Pg screw connection               | Pg11                    |
| Material (Housing)                | GD-Zn                   |
| Material (Housing surface)        | Ni                      |
| Material (Rotating parts)         | CuZn                    |
| Degree of protection (plugged in) | IP65<br>IP67<br>IP68    |

# RC-12P1N8A1200 - Cable connector

1597468

<https://www.phoenixcontact.com/us/products/1597468>

## Drawings

Schematic diagram



Connector pin assignment

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)