

# RC-12P2S1290EH - Coupler connector



1598365

<https://www.phoenixcontact.com/us/products/1598365>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, Direction of rotation: Counter direction, contact connection type: Pin, Solder cup, cable diameter range: 7.5 mm ... 9.5 mm, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240947

## Commercial data

Item number	1598365
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356220477
Weight per piece (including packing)	76.235 g
Weight per piece (excluding packing)	69.45 g
Country of origin	DE

# RC-12P2S1290EH - Coupler connector



1598365

<https://www.phoenixcontact.com/us/products/1598365>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	7.5 mm ... 9.5 mm
Seal material	NBR

# RC-12P2S1290EH - Coupler connector

1598365

<https://www.phoenixcontact.com/us/products/1598365>



Drawings

# RC-12P2S1290EH - Coupler connector



1598365

<https://www.phoenixcontact.com/us/products/1598365>

## Classifications

### ECLASS

ECLASS-13.0

27440116

### UNSPSC

UNSPSC 21.0

39121400

# RC-12P2S1290EH - Coupler connector



1598365

<https://www.phoenixcontact.com/us/products/1598365>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5877b8b5-924a-49cc-8333-ec991e3d4517

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)