

# RC-19P1N127300 - Crimp contact



1602544

<https://www.phoenixcontact.com/us/products/1602544>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimp contact



The figure shows the 12-pos. product version, with standard DIN cable gland

## Commercial data

Item number	1602544
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356240239
Weight per piece (including packing)	81.63 g
Weight per piece (excluding packing)	81.63 g
Country of origin	DE

# RC-19P1N127300 - Crimp contact



1602544

<https://www.phoenixcontact.com/us/products/1602544>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Material specifications

Flammability rating according to UL 94	V0
--	----

# RC-19P1N127300 - Crimp contact



1602544

<https://www.phoenixcontact.com/us/products/1602544>

## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-19P1N127300 - Crimp contact



1602544

<https://www.phoenixcontact.com/us/products/1602544>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)