

RC-19S1NRA80EN - Cable connector



1602982

<https://www.phoenixcontact.com/us/products/1602982>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, straight, Screw locking mechanism, Crimp connection, cable diameter range: 3 mm ... 10.5 mm

The figure shows the 12-pos. product version

Commercial data

Item number	1602982
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356242721
Weight per piece (including packing)	77.68 g
Weight per piece (excluding packing)	69.95 g
Country of origin	DE

RC-19S1NRA80EN - Cable connector



1602982

<https://www.phoenixcontact.com/us/products/1602982>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Connection method	Crimp connection
Application	Signal

Housing

Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65
	IP67
	IP68

Seal

External cable diameter	3 mm ... 10.5 mm
Seal material	NBR

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com