

RC-1LS1N120000 - Contact insert



1603004

<https://www.phoenixcontact.com/us/products/1603004>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, contact connection type: Socket, Solder cup

Commercial data

Item number	1603004
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABRAFU
GTIN	4046356242875
Weight per piece (including packing)	6.99 g
Weight per piece (excluding packing)	6.99 g
Country of origin	DE

RC-1LS1N120000 - Contact insert



1603004

<https://www.phoenixcontact.com/us/products/1603004>

Technical data

Product properties

Product type	Contact insert
Application	Signal
Number of positions	19
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1.5 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	10 A (for max. connection cross section)
Nominal voltage U _N	150 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A (for max. connection cross section)
Nominal voltage U _N	150 V
Overvoltage category	II
Degree of pollution	3

Connection data

Connection method	Solder cup
-------------------	------------

Connector

Direction of rotation	Standard
-----------------------	----------

RC-1LS1N120000 - Contact insert



1603004

<https://www.phoenixcontact.com/us/products/1603004>

Classifications

ECLASS

ECLASS-13.0

27440223

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com