

RC-2RP1N12RDEP - Cable connector



1603370

<https://www.phoenixcontact.com/us/products/1603370>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 11+PE, Direction of rotation: Standard, contact connection type: Pin, Solder cup, cable diameter range: 3 mm ... 10.5 mm, coding: N

The figure shows the 12-pos. product version, with double bracket strain relief

Commercial data

Item number	1603370
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356245135
Weight per piece (including packing)	134.97 g
Weight per piece (excluding packing)	134.97 g
Country of origin	DE

RC-2RP1N12RDEP - Cable connector



1603370

<https://www.phoenixcontact.com/us/products/1603370>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Connector

Insulating body

Coding	N
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	11+PE
Number (Contact group 1)	1
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	11
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A

Housing

Order information:	Order contact inserts and cable clamping/shield accessories separately
Type	Cable connector housing
Thread type	M23
Design	straight

RC-2RP1N12RDEP - Cable connector



1603370

<https://www.phoenixcontact.com/us/products/1603370>

Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Screw mounting (Pg13,5)
Housing material	Metal
Degree of protection (plugged in)	IP67

Seal

External cable diameter	3 mm ... 10.5 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-2RP1N12RDEP - Cable connector



1603370

<https://www.phoenixcontact.com/us/products/1603370>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-2RP1N12RDEP - Cable connector



1603370

<https://www.phoenixcontact.com/us/products/1603370>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f18d3331-2808-4380-9284-7cb587f16b2e

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com