

RC-2RS1N120000 - Contact insert



1603405

<https://www.phoenixcontact.com/us/products/1603405>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 11+PE, contact connection type: Socket, Solder cup, series: NC, RC, RM, TU, UC

The figure shows the 6-pos. product version

Commercial data

Item number	1603405
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABRAFU
GTIN	4046356245319
Weight per piece (including packing)	9.11 g
Weight per piece (excluding packing)	9.11 g
Country of origin	DE

RC-2RS1N120000 - Contact insert



1603405

<https://www.phoenixcontact.com/us/products/1603405>

Technical data

Notes

Order information:	Order 12 x 1 mm crimp contacts separately
--------------------	---

Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	12
Connection profile	11+PE
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Solder cup
-------------------	------------

Connector

Direction of rotation	Standard
-----------------------	----------

RC-2RS1N120000 - Contact insert



1603405

<https://www.phoenixcontact.com/us/products/1603405>

Drawings

Schematic diagram



Connector pin assignment

RC-2RS1N120000 - Contact insert



1603405

<https://www.phoenixcontact.com/us/products/1603405>

Classifications

ECLASS

ECLASS-13.0

27440223

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com