

# RC-2RS1N1290G0 - Coupler connector



1603431

<https://www.phoenixcontact.com/us/products/1603431>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 11+PE, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N

## Commercial data

Item number	1603431
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356245395
Weight per piece (including packing)	70.67 g
Weight per piece (excluding packing)	66.921 g
Country of origin	DE

# RC-2RS1N1290G0 - Coupler connector



1603431

<https://www.phoenixcontact.com/us/products/1603431>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order 12 x 1 mm crimp contacts separately
Coding	N
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	11+PE
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	1 mm <sup>2</sup>
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	II
Degree of pollution	3

#### Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

# RC-2RS1N1290G0 - Coupler connector



1603431

<https://www.phoenixcontact.com/us/products/1603431>

## Drawings

Schematic diagram



Connector pin assignment

# RC-2RS1N1290G0 - Coupler connector

1603431

<https://www.phoenixcontact.com/us/products/1603431>

Schematic diagram



Connector pin assignment

# RC-2RS1N1290G0 - Coupler connector



1603431

<https://www.phoenixcontact.com/us/products/1603431>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-2RS1N1290G0 - Coupler connector



1603431

<https://www.phoenixcontact.com/us/products/1603431>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)