RC-Z2196 - Cable gland

1604338

https://www.phoenixcontact.com/us/products/1604338

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, external cable diameter 7 mm ... 10.5 mm, shielding: no, connecting thread: Pg11, series: RC

Commercial data

Item number	1604338
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356248860
Weight per piece (including packing)	30.69 g
Weight per piece (excluding packing)	28.15 g
Customs tariff number	74198090
Country of origin	DE

Technical data

Product properties

Product type	Cable screw gland
Series	RC
Shielded	no

Dimensions

Thread type connection side	Pg11

Material specifications

Color	brass color
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter	7 mm ... 10.5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68

Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 10.0	EC000441

UNSPSC

UNSPSC 21.0	39121300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cb0abcb0-975b-49a6-ab51-9af0c55d2f64

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com