RC-Z2462 - Cable clamp type cage and shield adapter

1604558

https://www.phoenixcontact.com/us/products/1604558

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable clamp type cage and shield adapter, shielded: yes, cable diameter range: 2 mm ... 10.5 mm, series: NC, RC, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0. 1 %)

Commercial data

Item number	1604558
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356249874
Weight per piece (including packing)	9.94 g
Weight per piece (excluding packing)	5.913 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Cable clamp type cage
Series	NC
	RC
Type of the screw connection	Universal with shield
Shielded	yes

Cable/line

External cable diameter	2 mm ... 10.5 mm

Mechanical properties

Mechanical data

Type of the screw connection	Universal with shield

Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 10.0	EC000441

UNSPSC

UNSPSC 21.0	39121300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com