

SM-5EP1N8A9L03 - Coupler connector



1605779

<https://www.phoenixcontact.com/us/products/1605779>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, application: Power, straight long, Screw locking mechanism, M40, number of positions: 2+3+PE, contact connection type: Pin, shielded: yes, cable diameter range: 12.5 mm .. 17 mm, number of positions: 6, connection method: Crimp connection, series: SM

Commercial data

Item number	1605779
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABRBGG
GTIN	4046356254731
Weight per piece (including packing)	569 g
Weight per piece (excluding packing)	297.19 g
Customs tariff number	85366990
Country of origin	DE

SM-5EP1N8A9L03 - Coupler connector



1605779

<https://www.phoenixcontact.com/us/products/1605779>

Technical data

Notes

Order information:	Order crimp contacts 4 x Ø 2 mm, 4 x Ø 3.6 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
Series	SM
Application	Power
Number of positions	6
Connection profile	2+3+PE
Shielded	yes
Thread type	M40

Connection data

Conductor connection

Connection method	Crimp connection
-------------------	------------------

Electrical properties

Contact: Contact group 1

Contact diameter	3.6 mm
Nominal current I_N	70 A
Nominal voltage U_N	630 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

Contact: Contact group 2

Contact diameter	2 mm
Nominal current I_N	30 A
Nominal voltage U_N	250 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	4 kV

Connector

Type	straight long
------	---------------

Cable/line

External cable diameter	12.5 mm ... 17 mm
-------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

SM-5EP1N8A9L03 - Coupler connector



1605779

<https://www.phoenixcontact.com/us/products/1605779>

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	3000 m

SM-5EP1N8A9L03 - Coupler connector




1605779

<https://www.phoenixcontact.com/us/products/1605779>

Drawings

Schematic diagram



Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com