

TU-16P1N8ATUAB - Cable connector



1605981

<https://www.phoenixcontact.com/us/products/1605981>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: TU, angled, shielded: yes, Bayonet locking, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 9.5 mm ... 11.5 mm, coding: N

Commercial data

Item number	1605981
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAHC
GTIN	4046356256377
Weight per piece (including packing)	166.62 g
Weight per piece (excluding packing)	166.62 g
Country of origin	DE

TU-16P1N8ATUAB - Cable connector



1605981

<https://www.phoenixcontact.com/us/products/1605981>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	16
Direction of rotation	Standard
Connection profile	16
Number (Contact group 1)	16
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Bayonet locking
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

Seal

External cable diameter	9.5 mm ... 11.5 mm
Seal material	FPM

TU-16P1N8ATUAB - Cable connector




1605981

<https://www.phoenixcontact.com/us/products/1605981>

Drawings

Schematic diagram




Connector pin assignment

TU-16P1N8ATUAB - Cable connector



1605981

<https://www.phoenixcontact.com/us/products/1605981>



TU-16P1N8ATUAB - Cable connector



1605981

<https://www.phoenixcontact.com/us/products/1605981>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com