

# UC-09P1N8AT0DU - Cable connector



1606234

<https://www.phoenixcontact.com/us/products/1606234>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, application: Signal, series: UC, angled, shielded: yes, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 2 mm ... 14.5 mm, coding: N



The figure shows the 12-pos. product version

## Commercial data

Item number	1606234
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIC
GTIN	4046356258258
Weight per piece (including packing)	160 g
Weight per piece (excluding packing)	160 g
Country of origin	DE

# UC-09P1N8AT0DU - Cable connector



1606234

<https://www.phoenixcontact.com/us/products/1606234>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

#### Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

#### Seal

# UC-09P1N8AT0DU - Cable connector



1606234

<https://www.phoenixcontact.com/us/products/1606234>

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

# UC-09P1N8AT0DU - Cable connector




1606234

<https://www.phoenixcontact.com/us/products/1606234>

## Drawings

Schematic diagram



Connector pin assignment

# UC-09P1N8AT0DU - Cable connector

1606234

<https://www.phoenixcontact.com/us/products/1606234>



Schematic diagram




Connector pin assignment

# UC-09P1N8AT0DU - Cable connector



1606234

<https://www.phoenixcontact.com/us/products/1606234>



Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)