

UC-12S2N8A80AB - Cable connector



1606417

<https://www.phoenixcontact.com/us/products/1606417>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: UC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Socket, Crimp connection, cable diameter range: 9.5 mm ... 11.5 mm, coding: N

The figure shows the 12-pos. product version with standard contact chamber numbering

Commercial data

Item number	1606417
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIA
GTIN	4046356259408
Weight per piece (including packing)	87.56 g
Weight per piece (excluding packing)	87.56 g
Country of origin	DE

UC-12S2N8A80AB - Cable connector



1606417

<https://www.phoenixcontact.com/us/products/1606417>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

Seal

External cable diameter	9.5 mm ... 11.5 mm
Seal material	FPM

UC-12S2N8A80AB - Cable connector



1606417

<https://www.phoenixcontact.com/us/products/1606417>

Drawings

Schematic diagram



Connector pin assignment

UC-12S2N8A80AB - Cable connector

1606417

<https://www.phoenixcontact.com/us/products/1606417>

Schematic diagram



Connector pin assignment

UC-12S2N8A80AB - Cable connector



1606417

<https://www.phoenixcontact.com/us/products/1606417>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UC-12S2N8A80AB - Cable connector



1606417

<https://www.phoenixcontact.com/us/products/1606417>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com