

# VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame, IP67, for push-pull interlocking, plastic, with the Freenet system, for square panel cutout, with grommet, without mounting screws

## Commercial data

Item number	1608197
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNODB
GTIN	4046356159937
Weight per piece (including packing)	8.5 g
Weight per piece (excluding packing)	8.4 g
Customs tariff number	85389099
Country of origin	DE

# VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

## Technical data

### Product properties

Product type	Panel-mount frame
Application	Freenet
Type	Version 14
Number of positions	8
Connection profile	RJ45

### Insulation characteristics

Degree of pollution	2
---------------------	---

### Electrical properties


Transmission medium	Copper
---------------------	--------

### Connection data

#### Connection technology

Connection method	Spring-cage connection
-------------------	------------------------

### Dimensions

Dimensional drawing	
Width	29.5 mm
Height	42 mm
Length	37 mm

### Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR
Seal material, flat gasket	NBR
Housing material	Plastic
Housing surface material	PA, light gray
Contact surface material	Au/Ni
Contact carrier material	Polyester GF

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

# VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C

## Mounting

Mounting type	Front mounting
---------------	----------------


# VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame

1608197

<https://www.phoenixcontact.com/us/products/1608197>



## Drawings



Mounting cutout

# VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

## Classifications

### ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

### ETIM

ETIM 10.0	EC002310
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)