

# VS-PPC-C2-MSTB-POBK-P13-B5-SP - Power connector



1608236

<https://www.phoenixcontact.com/us/products/1608236>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector, degree of protection: IP65, number of positions: 5, material: PA-GF, connection method: Spring-cage connection, connection cross section: AWG 18- 13, cable outlet: straight, color: black, Universal

## Commercial data

Item number	1608236
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABNOHA
GTIN	4046356159876
Weight per piece (including packing)	42.2 g
Weight per piece (excluding packing)	39.14 g
Customs tariff number	85366990
Country of origin	DE

# VS-PPC-C2-MSTB-POBK-P13-B5-SP - Power connector



1608236

<https://www.phoenixcontact.com/us/products/1608236>

## Technical data

### Product properties

Product type	Data plug
Sensor type	Universal
Number of positions	5
Connection profile	MSTB
Cable outlet	straight

### Insulation characteristics

Degree of pollution	2
---------------------	---

### Electrical properties

Rated voltage (III/3)	400 V
Rated current	16 A (at 20 °C)
Nominal voltage $U_N$	400 V
Nominal current $I_N$	16 A

### Connection data

Connection method	Spring-cage connection
-------------------	------------------------

### Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	PA-GF
Cable seal material	TPE
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PA

### Cable/line

External cable diameter	9 mm ... 13 mm
-------------------------	----------------

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP65

# VS-PPC-C2-MSTB-POBK-P13-B5-SP - Power connector



1608236

<https://www.phoenixcontact.com/us/products/1608236>

Ambient temperature (operation)

-40 °C ... 70 °C

# VS-PPC-C2-MSTB-POBK-P13-B5-SP - Power connector




1608236

<https://www.phoenixcontact.com/us/products/1608236>


## Drawings

Dimensional drawing



Push-Pull connector

Schematic diagram



Connector pin assignment for PROFINET Push-Pull, power connector, 400 V

# VS-PPC-C2-MSTB-POBK-P13-B5-SP - Power connector



1608236

<https://www.phoenixcontact.com/us/products/1608236>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)