

# RC-06P1N1290EJ - Coupler connector



1615780

<https://www.phoenixcontact.com/us/products/1615780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.  
product version

M23, Coupler connector, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder cup, cable diameter range: 6.5 mm ... 7.5 mm, coding: N

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1615780                        |
| Packing unit                         | 20 pc                          |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ABRAFG                         |
| GTIN                                 | 4046356669221                  |
| Weight per piece (including packing) | 75.95 g                        |
| Weight per piece (excluding packing) | 75.95 g                        |
| Country of origin                    | DE                             |

# RC-06P1N1290EJ - Coupler connector



1615780

<https://www.phoenixcontact.com/us/products/1615780>

## Technical data

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|   |  |
|---|--|
| Coding  | N  |
| Material (Insulating body)                      | PBT                                      |
| Material (Contact)                              | CuZn                                     |
| Material (Contact surface)                      | Ni/Au                                    |
| Insertion/withdrawal cycles                     | 50                                       |
| Connection method                               | Solder cup                               |
| Contact switching type                          | Pin                                      |
| Application                                     | Signal                                   |
| Number of positions                             | 6  |
| Direction of rotation                           | Standard                                 |
| Connection profile                              | 6  |
| Number (Contact group 1)                        | 6  |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>                     |
| Litz wires Max. cross section (Contact group 1) | 2.5 mm <sup>2</sup>                      |
| Rated current Contact (Contact group 1)         | 20 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC                       |
| Rated surge voltage                             | 1.5 kV                                   |
| Overvoltage category                            | III                                      |
| Degree of pollution                             | 3  |

#### Housing

|                                   |                         |
|-----------------------------------|-------------------------|
| Type                              | Coupling housing        |
| Thread type                       | M23                     |
| Design                            | straight                |
| Type of locking                   | Screw locking mechanism |
| Pg screw connection               | none                    |
| Material (Housing)                | GD-Zn                   |
| Material (Housing surface)        | Ni                      |
| Material (Rotating parts)         | CuZn                    |
| Degree of protection (plugged in) | IP67                    |

#### Seal

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 6.5 mm ... 7.5 mm |
| Seal material           | NBR               |


# RC-06P1N1290EJ - Coupler connector

1615780

<https://www.phoenixcontact.com/us/products/1615780>

## Drawings

Schematic diagram



Connector pin assignment

# RC-06P1N1290EJ - Coupler connector



1615780

<https://www.phoenixcontact.com/us/products/1615780>

Schematic diagram



Dimensional drawing

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)