

# RF-17P1N8A90DUS - Coupler connector



1618027

<https://www.phoenixcontact.com/us/products/1618027>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, application: Feedback, signal, straight, SPEEDCON, M23, number of positions: 17, contact connection type: Pin, shielded: yes, cable diameter range: 5 mm ... 13.2 mm, number of positions: 17, connection method: Crimp connection, series: RF

## Commercial data

Item number	1618027
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAGG
GTIN	4046356630412
Weight per piece (including packing)	95 g
Weight per piece (excluding packing)	95 g
Country of origin	DE

# RF-17P1N8A90DUS - Coupler connector



1618027

<https://www.phoenixcontact.com/us/products/1618027>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Series	RF
Application	Feedback, signal Signal
Number of positions	17
Connection profile	17
Shielded	yes
Coding	N
Thread type	M23

### Material specifications

Seal material	FPM
Housing material	Metal

### Connection data

Conductor connection	
Connection method	Crimp connection

### Electrical properties

Contact	
Contact diameter	1 mm
Nominal current $I_N$	8 A
Nominal voltage $U_N$	100 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	50

### Connector

Type	straight
Direction of rotation	Standard

### Cable/line

External cable diameter	5 mm ... 13.2 mm
-------------------------	------------------

# RF-17P1N8A90DUS - Coupler connector



1618027

<https://www.phoenixcontact.com/us/products/1618027>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# RF-17P1N8A90DUS - Coupler connector




1618027

<https://www.phoenixcontact.com/us/products/1618027>

## Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), standard pin

# RF-17P1N8A90DUS - Coupler connector



1618027

<https://www.phoenixcontact.com/us/products/1618027>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)