

RC-06P1N120000N - Circular connector (cable-side)



1621120

<https://www.phoenixcontact.com/us/products/1621120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	1621120
Packing unit	30 pc
Minimum order quantity	30 pc
Note	Made to order (non-returnable)
Product key	ABRAFU
GTIN	4046356895842
Weight per piece (including packing)	7.95 g
Weight per piece (excluding packing)	7.95 g
Country of origin	DE

RC-06P1N120000N - Circular connector (cable-side)



1621120

<https://www.phoenixcontact.com/us/products/1621120>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number (Contact group 1)	6
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

RC-06P1N120000N - Circular connector (cable-side)



1621120

<https://www.phoenixcontact.com/us/products/1621120>

Drawings

Schematic diagram



Connector pin assignment

RC-06P1N120000N - Circular connector (cable-side)



1621120

<https://www.phoenixcontact.com/us/products/1621120>

Schematic diagram



Dimensional drawing

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com