

RC-12P2N122KYY - Device connector front mounting



1621734

<https://www.phoenixcontact.com/us/products/1621734>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Pin, Solder cup, Flat gasket, flange dimensions: 25 mm x 25 mm, coding: N

The figure shows the 12-pos. product version with standard contact chamber numbering

Commercial data

Item number	1621734
Packing unit	40 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFL
GTIN	4046356963671
Weight per piece (including packing)	26.85 g
Weight per piece (excluding packing)	26.85 g
Country of origin	DE

RC-12P2N122KYY - Device connector front mounting



1621734

<https://www.phoenixcontact.com/us/products/1621734>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Order information:	Order contact inserts separately
Type	Flange housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Front mounting/square flange (4x Ø 2.7 mm)
Flange dimensions	25 mm x 25 mm
Housing material	GD-Zn
Degree of protection (plugged in)	IP67
Seal for the device	Flat gasket

RC-12P2N122KYY - Device connector front mounting

1621734

<https://www.phoenixcontact.com/us/products/1621734>

Drawings



Installation dimensions



Installation dimensions

RC-12P2N122KYY - Device connector front mounting



1621734

<https://www.phoenixcontact.com/us/products/1621734>

Schematic diagram



Connector pin assignment


RC-12P2N122KYY - Device connector front mounting



1621734

<https://www.phoenixcontact.com/us/products/1621734>

Schematic diagram



Technical drawings can be found under Downloads

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com