

HC-26S1N8A0000 - Contact insert



1623270

<https://www.phoenixcontact.com/us/products/1623270>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M27, number of positions: 26, contact connection type: Socket, Crimp connection, series: HC

Commercial data

Item number	1623270
Packing unit	100 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJT
GTIN	4055626272931
Weight per piece (including packing)	3.98 g
Weight per piece (excluding packing)	3.854 g
Customs tariff number	85472000
Country of origin	DE

HC-26S1N8A0000 - Contact insert



1623270

<https://www.phoenixcontact.com/us/products/1623270>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Contact insert
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Coding	N
Thread type	M27

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Connector

Direction of rotation	Standard
-----------------------	----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 125 °C
---------------------------------	-------------------

HC-26S1N8A0000 - Contact insert




1623270

<https://www.phoenixcontact.com/us/products/1623270>

Drawings

Schematic diagram



Connector pin assignment

HC-26S1N8A0000 - Contact insert



1623270

<https://www.phoenixcontact.com/us/products/1623270>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-26S1N8A0000 - Contact insert



1623270

<https://www.phoenixcontact.com/us/products/1623270>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com