

# HC-28S1N12F3DU - Coupler connector



1624750

<https://www.phoenixcontact.com/us/products/1624750>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, application: Signal, straight, Screw locking mechanism, M27, contact connection type: Socket, number of positions: 28, connection method: Solder connection, series: HC

The figure shows the 26-pos.  
product version

## Commercial data

Item number	1624750
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	ABRAJG
GTIN	4055626299402
Weight per piece (including packing)	77.12 g
Weight per piece (excluding packing)	77.12 g
Country of origin	DE

# HC-28S1N12F3DU - Coupler connector



1624750

<https://www.phoenixcontact.com/us/products/1624750>

## Technical data

### Notes

Order information:	Order cable glands separately
--------------------	-------------------------------

### Product properties

Product type	Circular connector (cable-side)
Series	HC
Application	Signal
Number of positions	28
Coding	N
Thread type	M27

### Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal

### Connection data

#### Conductor connection

Connection method	Solder connection
-------------------	-------------------

### Electrical properties

#### Contact

Contact diameter	1 mm
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
Nominal voltage U <sub>N</sub>	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connector

Type	straight
Direction of rotation	Standard

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67, when plugged in
Ambient temperature (operation)	-20 °C ... 125 °C

# HC-28S1N12F3DU - Coupler connector

1624750

<https://www.phoenixcontact.com/us/products/1624750>



Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)