

CA-19P1N1280DUS - Cable connector



1627237

<https://www.phoenixcontact.com/us/products/1627237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 16+3, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding: N

The figure shows the 12-pos.
product version

Commercial data

Item number	1627237
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABRAEB
GTIN	4055626294216
Weight per piece (including packing)	84.83 g
Weight per piece (excluding packing)	84.83 g
Country of origin	DE

CA-19P1N1280DUS - Cable connector



1627237

<https://www.phoenixcontact.com/us/products/1627237>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Installation height	2000 m
Number (Contact group 1)	3
Contact diameter (Contact group 1)	1.5 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	16
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	SPEEDCON
Pg screw connection	none
Housing material	CuZn, GD-Zn

CA-19P1N1280DUS - Cable connector



1627237

<https://www.phoenixcontact.com/us/products/1627237>

Degree of protection (plugged in)	IP67
Seal	
External cable diameter	3 mm ... 14.5 mm
Seal material	FPM

CA-19P1N1280DUS - Cable connector



1627237

<https://www.phoenixcontact.com/us/products/1627237>

Drawings

Schematic diagram



Connector pin assignment

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com