

CA-000000085DU - Cable connector



1628040

<https://www.phoenixcontact.com/us/products/1628040>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, cable diameter range: 3 mm ... 14.5 mm

Commercial data

Item number	1628040
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABRAEE
GTIN	4055626377216
Weight per piece (including packing)	70.47 g
Weight per piece (excluding packing)	70.47 g
Country of origin	DE

CA-000000085DU - Cable connector



1628040

<https://www.phoenixcontact.com/us/products/1628040>

Technical data

Notes

Order information:	Order contact inserts separately
--------------------	----------------------------------

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	FPM

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com