

BS-MAGAZINE PROFILE L - Magazine mounting profile



1640723

<https://www.phoenixcontact.com/us/products/1640723>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mounting profile for magazines with marking area.

Commercial data

Item number	1640723
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BH21
Product key	BH2XX1
GTIN	4067923167155
Weight per piece (excluding packing)	185 g
Customs tariff number	39162000
Country of origin	DE

BS-MAGAZINE PROFILE L - Magazine mounting profile



1640723

<https://www.phoenixcontact.com/us/products/1640723>

Technical data

Dimensions

Width	51 mm
Height	21 mm
Length	988 mm

Material specifications

Color	black (RAL 9005)
Material	ABS

Environmental and real-life conditions

Ambient conditions

Optimum ambient temperature (storage/transport)	20.00 °C 60.00 % 2 years at 15°C ... 25°C and 50% ... 70% relative humidity
Ambient temperature (operation)	5 °C ... 35 °C
Ambient temperature (storage/transport)	0 °C ... 60 °C
Permissible humidity (operation)	10 % ... 80 %
Permissible humidity (storage/transport)	20 % ... 80 %
Resistance to UV radiation	Adhesive tape, UV-resistant, protect from direct sunlight during storage.

Mounting

Assembly note	Installation note: Taking the adhesive instructions into account, the L profile must only be installed in a horizontal mounting position. The surface must be sufficiently firm, smooth, and able to carry the required weight, e.g., stainless steel sheeting. Maximum weight load: 7 kg/10 cm width at 10° tilt, maximum. Adhesive instructions: The surfaces and joining pieces must be dry and clean. Avoid any condensation of moisture on the surfaces to be bonded. The joining pieces must be free of dust, grease, oil, and release agents. Loose paint or top layers must be removed or solidified. Apply pressure (10 N/cm² ... 15 N/cm², approximately) using a pressure roller or surface press. The curing time of the adhesive bonding is 24 hours.
---------------	--

BS-MAGAZINE PROFILE L - Magazine mounting profile



1640723

<https://www.phoenixcontact.com/us/products/1640723>

Classifications

ECLASS

ECLASS-13.0	21101030
ECLASS-15.0	21101030

ETIM

ETIM 10.0	EC011819
-----------	----------

UNSPSC

UNSPSC 21.0	22101500
-------------	----------

BS-MAGAZINE PROFILE L - Magazine mounting profile



1640723

<https://www.phoenixcontact.com/us/products/1640723>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com