

HC-M-DE-M25 - Pressure screw set

1647970

<https://www.phoenixcontact.com/us/products/1647970>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pressure screw set, for housing with M25 thread and glands, consisting of notched seal, 2 washers and pressure screw, cable diameter 8.5 - 18 mm, SW 25



Commercial data

Item number	1647970
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF68
Product key	AF7DFX
GTIN	4017918985141
Weight per piece (including packing)	18.82 g
Weight per piece (excluding packing)	17.08 g
Customs tariff number	74153300
Country of origin	DE

HC-M-DE-M25 - Pressure screw set



1647970

<https://www.phoenixcontact.com/us/products/1647970>

Technical data

Product properties

Product type	Half screw connection
No. of conductors	1
Shielded	no

Dimensions

Wrench size, union nut	25 mm
------------------------	-------

Material specifications

Material Pressure screw	Brass, nickel-plated
Seal material Cable seal	Perbunan

Cable/line

External cable diameter Cable 1	8.5 mm ... 18 mm
---------------------------------	------------------

Characteristics

Conductor sealing range	8.50 mm ... 18.00 mm
-------------------------	----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com