
# VS-08-A-RJ/MOD-F-IP67-SET-BU - Panel-mount frame

1652910

https://www.phoenixcontact.com/us/products/1652910

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame, IP67, with the Freenet system, for round panel cutout, with grommet, without mounting screws, with Freenet RJ45 socket insert, CAT5e, socket on socket

## Commercial data

| | |
|---|---|
| Item number | 1652910 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB17 |
| Product key | ABNNDA |
| GTIN | 4017918951269 |
| Weight per piece (including packing) | 23.8 g |
| Weight per piece (excluding packing) | 6.6 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Panel-mount frame |
| Application | Modular insert |
| Type | Version 6 |
| Connection profile | RJ45 |

### Electrical properties


| | |
|---|---|
| Transmission medium | Copper |

### Connection data

Connection technology

| | |
|---|---|
| Connection method | Screw connection |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 36 mm |
| Height | 36 mm |
| Length | 53.2 mm |

### Material specifications

| | |
|---|---|
| Flammability rating according to UL 94 | V0 |
| Seal material, flat gasket | NBR |
| Housing material | Plastic |

### Environmental and real-life conditions

Ambient conditions


| | |
|---|---|
| Degree of protection | IP67 |

### Mounting

| | |
|---|---|
| Mounting type | Front mounting |

## Drawings

Dimensional drawing




Mounting cutout

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440392 |
| ECLASS-15.0 | 27440318 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002597 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 1.021 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com