FBSW N 2-5/120MM - Wire bridge

1653821

https://www.phoenixcontact.com/us/products/1653821

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Wire bridge, number of positions: 1, nominal current: 17.5 A, length: 120 mm, color: red/black



Your advantages

- Flexible potential distribution, thanks to custom wire lengths
- Bridge terminal blocks of varying terminal widths with ease
- Easy, tool-free operation, thanks to plug-in contacts

Commercial data

Item number	1653821
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4067923187207
Weight per piece (including packing)	7.89 g
Weight per piece (excluding packing)	7.89 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Bridge
Number of positions	1

Insulation characteristics

Overvoltage category	III

Electrical properties

Maximum load current	17.5 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)

Connection data

Maximum load current	17.5 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)

Dimensions

Width	5.1 mm
Height	4.7 mm
Length	120 mm

Material specifications

Color	red/black
Material	CuSn
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mounting

Mounting type	Plug-in mounting

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com