

VS-ST-KX-50-RG58 - D-SUB coaxial contact



1655580

<https://www.phoenixcontact.com/us/products/1655580>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial contact, for D-SUB combination inserts, solder cup, socket, straight, for cable RG 58, gold-plated

Commercial data

Item number	1655580
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAC
GTIN	4046356029490
Weight per piece (including packing)	2.546 g
Weight per piece (excluding packing)	2.294 g
Customs tariff number	85366910
Country of origin	CZ

VS-ST-KX-50-RG58 - D-SUB coaxial contact



1655580

<https://www.phoenixcontact.com/us/products/1655580>

Technical data

Product properties

Product type	Contacts
Series	HC-M-04-KOAX
Contact material type	turned

Electrical properties


Rated current (Maximum load current)	2 A
Resistance (Insulation resistance)	$\geq 500 \text{ M}\Omega$

Connection data

Connection technology

Contact connection type	Coaxial
Connection method	Solder cup

Dimensions

Dimensional drawing	
Length [l]	26.8 mm
External cable diameter	5.2 mm

Material specifications

Material Contact	Metal
------------------	-------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
Insertion force	$\leq 7 \text{ N}$
Withdrawal force	$\leq 7 \text{ N}$

Characteristics

Measuring system

Resistance: Insulation resistance	$\geq 500 \text{ M}\Omega$
-----------------------------------	----------------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

Mounting

VS-ST-KX-50-RG58 - D-SUB coaxial contact



1655580

<https://www.phoenixcontact.com/us/products/1655580>

Mounting type

Solder connection

VS-ST-KX-50-RG58 - D-SUB coaxial contact




1655580

<https://www.phoenixcontact.com/us/products/1655580>

Drawings

Dimensional drawing



Cable connection

VS-ST-KX-50-RG58 - D-SUB coaxial contact



1655580

<https://www.phoenixcontact.com/us/products/1655580>

Classifications

ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

ETIM

ETIM 10.0	EC002943
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

VS-ST-KX-50-RG58 - D-SUB coaxial contact



1655580

<https://www.phoenixcontact.com/us/products/1655580>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bdd2840f-8ecd-41c9-bc00-ff3db642dc79

EF3.1 Climate Change

CO2e kg	0.729 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com