

VS-15-T-20-1-S-S - D-SUB sleeve housings



1655674

<https://www.phoenixcontact.com/us/products/1655674>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB sleeve housings, design: D-SUB 15, degree of protection: IP20, material: ABS, cable outlet: straight, housing size: 2, color: Bare metallic



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1655674 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | ABNCAE |
| GTIN | 4046356029568 |
| Weight per piece (including packing) | 19 g |
| Weight per piece (excluding packing) | 17.5 g |
| Customs tariff number | 85389099 |
| Country of origin | HU |

VS-15-T-20-1-S-S - D-SUB sleeve housings

1655674


<https://www.phoenixcontact.com/us/products/1655674>

Technical data

Product properties

| | |
|----------------------|-----------------|
| Product type | Sleeve housings |
| Type | D-SUB 15 |
| No. of cable outlets | 1 |
| Cable outlet | straight |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 40 mm |
| Height | 15.2 mm |
| Length | 34.7 mm |

Material specifications

| | |
|--|---------------|
| Color | Bare metallic |
| Flammability rating according to UL 94 | V0 |
| Housing material | ABS |
| Housing surface material | metal-plated |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 4 mm ... 8.5 mm |
|-------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 90 °C |

VS-15-T-20-1-S-S - D-SUB sleeve housings




1655674

<https://www.phoenixcontact.com/us/products/1655674>

Drawings

Dimensional drawing



VS-15-T-20-1-S-S - D-SUB sleeve housings



1655674

<https://www.phoenixcontact.com/us/products/1655674>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com