

# HC-D 25-AP-GY - Cover plate



1660355

<https://www.phoenixcontact.com/us/products/1660355>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON cover plate, for wall cutouts of type D25, 3.5 mm thick, gray



## Commercial data

Item number	1660355
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF66
Product key	AF7AZD
GTIN	4017918021993
Weight per piece (including packing)	14.69 g
Weight per piece (excluding packing)	14.69 g
Customs tariff number	39269097
Country of origin	DE

# HC-D 25-AP-GY - Cover plate

1660355


<https://www.phoenixcontact.com/us/products/1660355>

## Technical data

### Product properties

Product type	Cover plate
Type	D25
Seal present	yes

### Dimensions

Dimensional drawing	
Width	45 mm
Height	3.5 mm
Length	103 mm
Drill hole distance, horizontal	86 mm
Drill hole distance, vertical	17.5 mm
Hole diameter	3.5 mm

### Installation dimensions

Width of the assembly cutout	24 mm
Length of the assembly cutout	74 mm

### Material specifications

Material	PA
Flammability rating according to UL 94	HB
Seal material	PTS

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C


# HC-D 25-AP-GY - Cover plate

1660355

<https://www.phoenixcontact.com/us/products/1660355>



## Drawings



Dimensional drawing

# HC-D 25-AP-GY - Cover plate



1660355

<https://www.phoenixcontact.com/us/products/1660355>

## Classifications

### ECLASS

ECLASS-13.0	27440201
ECLASS-15.0	27440201

### ETIM

ETIM 10.0	EC002309
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-D 25-AP-GY - Cover plate



1660355

<https://www.phoenixcontact.com/us/products/1660355>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.366 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)