

HC-B 16-PR-DI - Profile gasket

1661079

<https://www.phoenixcontact.com/us/products/1661079>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile gasket for type B16 supporting base element



Commercial data

Item number	1661079
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF66
Product key	AF7AAZ
GTIN	4017918155506
Weight per piece (including packing)	5.51 g
Weight per piece (excluding packing)	5.41 g
Customs tariff number	40169300
Country of origin	DE

HC-B 16-PR-DI - Profile gasket



1661079

<https://www.phoenixcontact.com/us/products/1661079>

Technical data

Product properties

Product type	Seal
--------------	------

Material specifications

Material	NBR
----------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mounting

Assembly note	Profile gasket must be glued to the housing (e.g., Loctite 4204), not for ADVANCE housings or HC-...EMV housings.
---------------	---

HC-B 16-PR-DI - Profile gasket

1661079

<https://www.phoenixcontact.com/us/products/1661079>



Classifications

UNSPSC

UNSPSC 21.0	39131608
-------------	----------

HC-B 16-PR-DI - Profile gasket



1661079

<https://www.phoenixcontact.com/us/products/1661079>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com