

HC-DR-PG36 - Seal

1686614

<https://www.phoenixcontact.com/us/products/1686614>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Notched seals/2 washers, for pressure screws, type Pg36



Commercial data

Item number	1686614
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF68
Product key	AF7DFX
GTIN	4017918189839
Weight per piece (including packing)	22.38 g
Weight per piece (excluding packing)	22.38 g
Customs tariff number	40169300
Country of origin	DE

HC-DR-PG36 - Seal



1686614

<https://www.phoenixcontact.com/us/products/1686614>

Technical data

Product properties

Product type	Seal
Pg screw connection	Pg36

Material specifications

Seal material Cable seal	Perbunan
--------------------------	----------

Cable/line

External cable diameter	24 mm ... 33 mm
-------------------------	-----------------

Characteristics

Conductor sealing range	24.00 mm ... 33.00 mm
-------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

HC-DR-PG36 - Seal



1686614

<https://www.phoenixcontact.com/us/products/1686614>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com