VS-15-TI-2EMV - D-SUB EMC inner sleeve

1688065

https://www.phoenixcontact.com/us/products/1688065

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-Sub



D-SUB EMC inner sleeve, shell size 2, shielded, for sleeve housing VS-15-...

Commercial data

Item number	1688065
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AB19
Product key	ABNCBC
GTIN	4017918182304
Weight per piece (including packing)	24.45 g
Weight per piece (excluding packing)	24.23 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Product properties

Product type	Data connector (cable side)
Application	EMC inner sleeve
Type	D-SUB
Number of positions	15
Cable outlet	slanted

Electrical properties

Transmission medium	Copper

Connection data

Connection technology

Connection method	D-SUB

Interfaces

Signal type/category	Universal

Dimensions

Width	62.8 mm
Height	38.8 mm

Material specifications

Color	Bare metallic
Housing material	Metal

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440292

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.594 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com