

VS-15-TI-2EMV - D-SUB EMC inner sleeve

1688065

<https://www.phoenixcontact.com/us/products/1688065>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB EMC inner sleeve, shell size 2, shielded, for sleeve housing VS-15-...



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1688065 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | AB19 |
| Product key | ABNCBC |
| GTIN | 4017918182304 |
| Weight per piece (including packing) | 24.45 g |
| Weight per piece (excluding packing) | 24.23 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

1688065

<https://www.phoenixcontact.com/us/products/1688065>

Technical data

Product properties

| | |
|---------------------|-----------------------------|
| Product type | Data connector (cable side) |
| Application | EMC inner sleeve |
| Type | D-SUB |
| Number of positions | 15 |
| Cable outlet | slanted |

Electrical properties

| | |
|---------------------|--------|
| Transmission medium | Copper |
|---------------------|--------|

Connection data

Connection technology

| | |
|-------------------|-------|
| Connection method | D-SUB |
|-------------------|-------|

Interfaces

| | |
|----------------------|-----------|
| Signal type/category | Universal |
|----------------------|-----------|

Dimensions

| | |
|--------|---------|
| Width | 62.8 mm |
| Height | 38.8 mm |

Material specifications

| | |
|------------------|---------------|
| Color | Bare metallic |
| Housing material | Metal |

Cable/line

| | |
|----------------------|-----------|
| Signal type/category | Universal |
|----------------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

VS-15-TI-2EMV - D-SUB EMC inner sleeve



1688065

<https://www.phoenixcontact.com/us/products/1688065>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440290 |
| ECLASS-15.0 | 27440292 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

VS-15-TI-2EMV - D-SUB EMC inner sleeve



1688065

<https://www.phoenixcontact.com/us/products/1688065>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.594 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com