

# VS-15-ST-DSUB/16-MPT-0,5 - D-SUB contact insert




1688078

<https://www.phoenixcontact.com/us/products/1688078>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact insert, shell size 2, with 15 signal contacts, male type of contact, screw connection, straight, for panel mounting frame and sleeve housing with IP67 protection



## Your advantages

- Screw connection

## Commercial data

Item number	1688078
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4017918179564
Weight per piece (including packing)	17.27 g
Weight per piece (excluding packing)	15.1 g
Customs tariff number	85366990
Country of origin	DE

# VS-15-ST-DSUB/16-MPT-0,5 - D-SUB contact insert



1688078

<https://www.phoenixcontact.com/us/products/1688078>

## Technical data

### Product properties

Product type	Contact insert
Application	Combination contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Shielded	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	60 V
Rated current	5 A
Insulation resistance	$\geq 5000 \text{ M}\Omega$
Contact resistance per contact pair	$\leq 2.5 \text{ m}\Omega$
Transmission medium	Copper

### Connection data

Connection method	Screw connection
-------------------	------------------

### Dimensions

Width	39.3 mm
Height	12.6 mm
Length	48 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel
Housing surface material	tin-plated
Contact material	Copper alloy
Contact surface material	Au/Ni

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\leq 200$
Insertion force per signal contact	$\leq 3.30 \text{ N}$
Extraction force per signal contact	$\leq 2.2 \text{ N}$

### Environmental and real-life conditions

# VS-15-ST-DSUB/16-MPT-0,5 - D-SUB contact insert



1688078

<https://www.phoenixcontact.com/us/products/1688078>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

## Mounting

Mounting type	Hole
---------------	------

# VS-15-ST-DSUB/16-MPT-0,5 - D-SUB contact insert



1688078

<https://www.phoenixcontact.com/us/products/1688078>

## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 10.0	EC001132
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1688078

<https://www.phoenixcontact.com/us/products/1688078>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	68c12945-45a9-433b-9009-2386a8d401bf

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)